

9071.2701

Product number

Actuation type	direct	
Weight	1.400 g	
Switching function	Changeover switch with OFF position in the center (SPDT - Center OFF)	
Material fixed contact	CuZn gold-plated	
Number of poles	1 - pole	
Connections	PCB terminal, injected in base sealed with epoxy resin angled 90° parallel to lever tilt direction	
Contact system	5E4	
Rating IEC	<= 0.4V A 28 V	
Contact resistance (new condition)	< 50 mOhm	
Insulation resistance (new condition)	> 500 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 500 V
Actuators	lever, CurZn nickel-plated, lever 6.3 long	

Housing description	housing: gray, PA glass fiber-reinforced, for round device cut-out with additional fastening bracket of CuSn base plate: gray, PA glass fiber-reinforced	
Connection surface	Bearing connection External connection	gold plated gold plated
Contact material	CuSn gold-plated	
Contact type	slide contact	
Type of fastening	pcb assembly	

All information subject to possible technical changes