



PART NO.	ENG. NO.
26-01-3169	4573-A228



CONTACT POINT




MIN. TO TERMINAL
CONTACT POINT FROM
BOTTOM OF CARD SLOT





3.78
.149

TERMINALS SHOWN IN
4338 SERIES HOUSING

- NOTES:
1. MATERIAL: BRASS ALLOY, 0.25/.010 THICK.
 2. FINISH:
228: 0.00076/.000030 MIN. SELECT GOLD ON CONTACT AREA,
0.00254/.000100 MIN. SELECT MATTE TIN IN CRIMP AREA,
BOTH OVER 0.00127/.000050 MIN. NICKEL OVERALL.
 3. PRODUCT SPECIFICATION: PS-09-50
 4. TERMINAL FOR USE WITH 24-30 AWG. WIRE.
 5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
COSMETIC SPECIFICATION PS-45499-002.
 6. FOR USE WITH 4338 HOUSING.




SECTION Z-Z




LEGEND

- 4573-***
- CANTILEVER STYLE
BLANK = STANDARD
A = INCREASED WIPE
- FORM
BLANK = CHAIN
L = LOOSE
- PLATING
SEE NOTE 2



SECTION Y-Y
SCALE 10:1



SECTION X-X
SCALE 10:1

ADD FRONT ANGLE EC NO: UCP2013-2174 DRWN:MKIPPER CH'KD:SSOUSEK APPR:FSMITH				DESCRIPTION REV	QUALITY SYMBOLS ▽ =0 ▽ =0 ▽ =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm			INCH	DRAWN BY MKIPPER		DATE 2010/4/21		TITLE KK .156 CRIMP TERMINAL FOR EDGE CARD CONNECTOR INCREASED WIPE LENGTH molex				
			3 PLACES			± ---	± .010	CHECKED BY SSOUSEK		DATE 2010/04/21					
			2 PLACES			± 0.25	± .014	APPROVED BY FSMITH		DATE 2012/04/19					
			1 PLACE			± 0.36	± ---								
			0 PLACE			± ---	± ---								
			ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.				SHEET NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		RSD-4573-001				1 OF 1			
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								