

**MANUFACTURER'S PART NUMBER**

GCM-KIT-COG-DE-A

Class 1 Automotive AEC-Q200 qualified

**KIT CONTENTS****QTY IN KIT****SPECIFICATIONS**

|                    |    |                                    |
|--------------------|----|------------------------------------|
| GCM1555C1HR30WA16D | 20 | 0402(1005M) COG 0.30pF ±0.05pF 50V |
| GCM1555C1HR40WA16D | 20 | 0402(1005M) COG 0.40pF ±0.05pF 50V |
| GCM1555C1HR50WA16D | 20 | 0402(1005M) COG 0.50pF ±0.05pF 50V |
| GCM1555C1HR60WA16D | 20 | 0402(1005M) COG 0.60pF ±0.05pF 50V |
| GCM1555C1HR70WA16D | 20 | 0402(1005M) COG 0.70pF ±0.05pF 50V |
| GCM1555C1HR80WA16D | 20 | 0402(1005M) COG 0.80pF ±0.05pF 50V |
| GCM1555C1HR90WA16D | 20 | 0402(1005M) COG 0.90pF ±0.05pF 50V |
| GCM1555C1H1R0BA16D | 20 | 0402(1005M) COG 1.0pF ±0.1pF 50V   |
| GCM1555C1H2R0BA16D | 20 | 0402(1005M) COG 2.0pF ±0.1pF 50V   |
| GCM1555C1H3R0BA16D | 20 | 0402(1005M) COG 3.0pF ±0.1pF 50V   |
| GCM1555C1H4R0BA16D | 20 | 0402(1005M) COG 4.0pF ±0.1pF 50V   |
| GCM1555C1H5R0BA16D | 20 | 0402(1005M) COG 5.0pF ±0.1pF 50V   |
| GCM1555C1H6R0BA16D | 20 | 0402(1005M) COG 6.0pF ±0.1pF 50V   |
| GCM1555C1H7R0BA16D | 20 | 0402(1005M) COG 7.0pF ±0.1pF 50V   |
| GCM1555C1H8R0BA16D | 20 | 0402(1005M) COG 8.0pF ±0.1pF 50V   |
| GCM1555C1H9R0BA16D | 20 | 0402(1005M) COG 9.0pF ±0.1pF 50V   |
| GCM1555C1H100JA16D | 20 | 0402(1005M) COG 10pF ±5% 50V       |
| GCM1555C1H120JA16D | 20 | 0402(1005M) COG 12pF ±5% 50V       |
| GCM1555C1H150JA16D | 20 | 0402(1005M) COG 15pF ±5% 50V       |
| GCM1555C1H180JA16D | 20 | 0402(1005M) COG 18pF ±5% 50V       |
| GCM1555C1H220JA16D | 20 | 0402(1005M) COG 22pF ±5% 50V       |
| GCM1555C1H270JA16D | 20 | 0402(1005M) COG 27pF ±5% 50V       |
| GCM1555C1H330JA16D | 20 | 0402(1005M) COG 33pF ±5% 50V       |
| GCM1555C1H390JA16D | 20 | 0402(1005M) COG 39pF ±5% 50V       |
| GCM1555C1H470JA16D | 20 | 0402(1005M) COG 47pF ±5% 50V       |
| GCM1555C1H560JA16D | 20 | 0402(1005M) COG 56pF ±5% 50V       |
| GCM1555C1H680JA16D | 20 | 0402(1005M) COG 68pF ±5% 50V       |
| GCM1555C1H820JA16D | 20 | 0402(1005M) COG 82pF ±5% 50V       |
| GCM1555C1H101JA16D | 20 | 0402(1005M) COG 100pF ±5% 50V      |
| GCM1555C1H121JA16D | 20 | 0402(1005M) COG 120pF ±5% 50V      |
| GCM1555C1H151JA16D | 20 | 0402(1005M) COG 150pF ±5% 50V      |
| GCM1555C1H181JA16D | 20 | 0402(1005M) COG 180pF ±5% 50V      |
| GCM1555C1H221JA16D | 20 | 0402(1005M) COG 220pF ±5% 50V      |
| GCM1555C1H271JA16D | 20 | 0402(1005M) COG 270pF ±5% 50V      |
| GCM1555C1H331JA16D | 20 | 0402(1005M) COG 330pF ±5% 50V      |
| GCM1555C1H391JA16D | 20 | 0402(1005M) COG 390pF ±5% 50V      |
| GCM1555C1H471JA16D | 20 | 0402(1005M) COG 470pF ±5% 50V      |
| GCM1555C1H561JA16D | 20 | 0402(1005M) COG 560pF ±5% 50V      |
| GCM1555C1H681JA16D | 20 | 0402(1005M) COG 680pF ±5% 50V      |
| GCM1555C1H821JA16D | 20 | 0402(1005M) COG 820pF ±5% 50V      |
| GCM1555C1H102JA16D | 20 | 0402(1005M) COG 1000pF ±5% 50V     |