

MANUFACTURER'S PART NUMBER

GRM02-KIT-TTOL-DE

KIT DESCRIPTION

01005 Class 1 Tight Tolerance

KIT CONTENTS**QTY IN KIT****SPECIFICATIONS**

GRM0225C1HR20WA03L
GRM0225C1HR30WA03L
GRM0225C1HR40WA03L
GRM0225C1HR50WA03L
GRM0225C1HR60WA03L
GRM0225C1HR70WA03L
GRM0225C1HR80WA03L
GRM0225C1HR90WA03L
GRM0225C1H1R0WA03L
GRM0225C1H1R1BA03L
GRM0225C1H1R2BA03L
GRM0225C1H1R3BA03L
GRM0225C1H1R4BA03L
GRM0225C1H1R5BA03L
GRM0225C1H1R6BA03L
GRM0225C1H1R7BA03L
GRM0225C1H1R8BA03L
GRM0225C1H1R9BA03L
GRM0225C1H2R0BA03L
GRM0225C1H2R1BA03L
GRM0225C1H2R2BA03L
GRM0225C1H2R3BA03L
GRM0225C1H2R4BA03L
GRM0225C1H2R5BA03L
GRM0225C1H2R6BA03L
GRM0225C1H2R7BA03L
GRM0225C1H2R8BA03L
GRM0225C1H2R9BA03L
GRM0225C1H3R0BA03L
GRM0225C1H3R1BA03L
GRM0225C1H3R2BA03L
GRM0225C1H3R3BA03L
GRM0225C1H3R4BA03L
GRM0225C1H3R5BA03L
GRM0225C1H3R6BA03L
GRM0225C1H3R7BA03L
GRM0225C1H3R8BA03L
GRM0225C1H3R9BA03L
GRM0225C1H4R0BA03L
GRM0225C1H4R1BA03L
GRM0225C1H4R2BA03L
GRM0225C1H4R3BA03L
GRM0225C1H4R4BA03L
GRM0225C1H4R5BA03L

01005(0402M) COG 0.20pF ± 0.05 pF 50V
01005(0402M) COG 0.30pF ± 0.05 pF 50V
01005(0402M) COG 0.40pF ± 0.05 pF 50V
01005(0402M) COG 0.50pF ± 0.05 pF 50V
01005(0402M) COG 0.60pF ± 0.05 pF 50V
01005(0402M) COG 0.70pF ± 0.05 pF 50V
01005(0402M) COG 0.80pF ± 0.05 pF 50V
01005(0402M) COG 0.90pF ± 0.05 pF 50V
01005(0402M) COG 1.0pF ± 0.05 pF 50V
01005(0402M) COG 1.1pF ± 0.1 pF 50V
01005(0402M) COG 1.2pF ± 0.1 pF 50V
01005(0402M) COG 1.3pF ± 0.1 pF 50V
01005(0402M) COG 1.4pF ± 0.1 pF 50V
01005(0402M) COG 1.5pF ± 0.1 pF 50V
01005(0402M) COG 1.6pF ± 0.1 pF 50V
01005(0402M) COG 1.7pF ± 0.1 pF 50V
01005(0402M) COG 1.8pF ± 0.1 pF 50V
01005(0402M) COG 1.9pF ± 0.1 pF 50V
01005(0402M) COG 2.0pF ± 0.1 pF 50V
01005(0402M) COG 2.1pF ± 0.1 pF 50V
01005(0402M) COG 2.2pF ± 0.1 pF 50V
01005(0402M) COG 2.3pF ± 0.1 pF 50V
01005(0402M) COG 2.4pF ± 0.1 pF 50V
01005(0402M) COG 2.5pF ± 0.1 pF 50V
01005(0402M) COG 2.6pF ± 0.1 pF 50V
01005(0402M) COG 2.7pF ± 0.1 pF 50V
01005(0402M) COG 2.8pF ± 0.1 pF 50V
01005(0402M) COG 2.9pF ± 0.1 pF 50V
01005(0402M) COG 3.0pF ± 0.1 pF 50V
01005(0402M) COG 3.1pF ± 0.1 pF 50V
01005(0402M) COG 3.2pF ± 0.1 pF 50V
01005(0402M) COG 3.3pF ± 0.1 pF 50V
01005(0402M) COG 3.4pF ± 0.1 pF 50V
01005(0402M) COG 3.5pF ± 0.1 pF 50V
01005(0402M) COG 3.6pF ± 0.1 pF 50V
01005(0402M) COG 3.7pF ± 0.1 pF 50V
01005(0402M) COG 3.8pF ± 0.1 pF 50V
01005(0402M) COG 3.9pF ± 0.1 pF 50V
01005(0402M) COG 4.0pF ± 0.1 pF 50V
01005(0402M) COG 4.1pF ± 0.1 pF 50V
01005(0402M) COG 4.2pF ± 0.1 pF 50V
01005(0402M) COG 4.3pF ± 0.1 pF 50V
01005(0402M) COG 4.4pF ± 0.1 pF 50V
01005(0402M) COG 4.5pF ± 0.1 pF 50V

GRM0225C1H4R6BA03L
GRM0225C1H4R7BA03L
GRM0225C1H4R8BA03L
GRM0225C1H4R9BA03L
GRM0225C1H5R0BA03L
GRM0225C1H5R1BA03L
GRM0225C1H5R6BA03L
GRM0225C1H6R2BA03L
GRM0225C1H6R8BA03L
GRM0225C1H7R5BA03L
GRM0225C1H8R2BA03L
GRM0225C1H9R1BA03L
GRM0225C1H100GA03L
GRM0225C1H120GA03L
GRM0225C1H150GA03L
GRM0225C1H180GA02L
GRM0225C1H220GA02L
GRM0225C1H270GA02L
GRM0225C1H330GA02L
GRM0225C1H390GA02L
GRM0225C1H470GA02L
GRM0225C1H560GA02L
GRM0225C1H680GA02L
GRM0225C1H820GA02L
GRM0225C1H101GA02L
GRM0225C1E221GA02L

01005(0402M) C0G 4.6pF ± 0.1 pF 50V
01005(0402M) C0G 4.7pF ± 0.1 pF 50V
01005(0402M) C0G 4.8pF ± 0.1 pF 50V
01005(0402M) C0G 4.9pF ± 0.1 pF 50V
01005(0402M) C0G 5.0pF ± 0.1 pF 50V
01005(0402M) C0G 5.1pF ± 0.1 pF 50V
01005(0402M) C0G 5.6pF ± 0.1 pF 50V
01005(0402M) C0G 6.2pF ± 0.1 pF 50V
01005(0402M) C0G 6.8pF ± 0.1 pF 50V
01005(0402M) C0G 7.5pF ± 0.1 pF 50V
01005(0402M) C0G 8.2pF ± 0.1 pF 50V
01005(0402M) C0G 9.1pF ± 0.1 pF 50V
01005(0402M) C0G 10pF $\pm 2\%$ 50V
01005(0402M) C0G 12pF $\pm 2\%$ 50V
01005(0402M) C0G 15pF $\pm 2\%$ 50V
01005(0402M) C0G 18pF $\pm 2\%$ 50V
01005(0402M) C0G 22pF $\pm 2\%$ 50V
01005(0402M) C0G 27pF $\pm 2\%$ 50V
01005(0402M) C0G 33pF $\pm 2\%$ 50V
01005(0402M) C0G 39pF $\pm 2\%$ 50V
01005(0402M) C0G 47pF $\pm 2\%$ 50V
01005(0402M) C0G 56pF $\pm 2\%$ 50V
01005(0402M) C0G 68pF $\pm 2\%$ 50V
01005(0402M) C0G 82pF $\pm 2\%$ 50V
01005(0402M) C0G 100pF $\pm 2\%$ 50V
01005(0402M) C0G 220pF $\pm 2\%$ 25V