




- 1




HOUSING MATERIAL: THERMOPLASTIC, COLOR-NATURAL.
- 2

CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3

CONTACT FINISH: .00127-.00254 [.000050-.000100] NICKEL UNDERPLATE ALL OVER; .00076 [.000030] GOLD PLATE IN CONTACT AREA, TIN PLATED POSTS.
- 4

ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK P.C. BOARD. RECOMMENDED P.C. BOARD HOLES ARE 1.151 [.0453] DIA PLATED THRU WITH 0.025-0.076 [.001-.003] COPPER, WITH 0.0076 [.0003] MIN TIN-LEAD PLATING; FINISHED HOLE AFTER PLATING 0.94-1.09 [.037-.043] DIA.
- 5

OBSOLETE



|                   |                   |                   |    |                   |    |                   |    |                    |                    |                    |      |             |
|-------------------|-------------------|-------------------|----|-------------------|----|-------------------|----|--------------------|--------------------|--------------------|------|-------------|
| 127.00<br>[5.000] | 128.90<br>[5.075] | 116.84<br>[4.600] | 46 | 116.84<br>[4.600] | 46 | 116.84<br>[4.600] | 46 | 374.65<br>[14.750] | 384.81<br>[15.150] | 392.43<br>[15.450] | 423  | 5533094-3   |
| 116.84<br>[4.600] | 118.74<br>[4.675] | 106.68<br>[4.200] | 42 | 106.68<br>[4.200] | 42 | 106.68<br>[4.200] | 42 | 344.17<br>[13.550] | 354.33<br>[13.950] | 361.95<br>[14.250] | 387  | 5533094-1   |
| L                 | K                 | J                 | H  | G                 | F  | E                 | D  | C                  | B                  | A                  | POSN | PART NUMBER |

RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

0 PLC  
1 PLC  
2 PLC  
3 PLC  
4 PLC  
ANGLES

± -  
± -  
± -  
± 0.13 [.005]  
± -  
± -

MATERIAL

12

3

DWN  
J. POLIGNONE  
11MAY05

CHK  
A. SHARPE  
11MAY05

APVD  
A. SHARPE  
11MAY05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

ASSEMBLY, PIN, VERTICAL, HDI, 3 ROW,  
TWO CENTER GUIDE PINS, 6.35[.250] ACTION PINS,  
.00076[.000030] GOLD PLATE

SIZE  
A1

CAGE CODE  
00779

DRAWING NO  
5533094

RESTRICTED TO

SCALE  
4:1

SHEET  
1 OF 1

REV  
02

4805 (3/11)