



NL8MMXX

8 pole speakON feedthrough coupler for cable extensions

Technical Information

Product	
Title	NL8MMXX
Connection Type	Adapter
Gender	male

Electrical	
Contact resistance	< 3 mΩ
Dielectric strength	1.5 kVac
Insulation resistance	> 0.1 GΩ (after dampheat)
Rated current per contact	25 A rms continuous
Rated voltage	250 V ac
Attention	speakON is NOT to be used as an mains or power supply connector (AC / DC)!

Mechanical	
Lifetime	> 5000 mating cycles
Locking device	Quick Lock

Material	
Contact plating	Ag
Contacts	Copper Alloy
Shell	Zinc diecast, black chrome plated
Insert	Polyamide (PA 6.6)

Environmental	
Temperature range	-30 °C to +80 °C
Flammability	UL 94 V-0