



DO NOT SCALE


D



6.15 DIA - 3 PLCS



INDEX CODE
-202-
(ALSO SEE HANDBOOK)




SEALING RIBS MUST BE
FREE OF DEFECTS.

12010718 - SEAL

CONN BODY - SEE CHART



FLEX AREA MAY EXHIBIT MATERIAL
SEPARATION AFTER FINAL ASSEMBLY

TERMINAL LOCK TO BE FOLDED
DOWN AS SHOWN AFTER
TERMINALS HAVE BEEN
INSERTED.




NOTES:

1. USE MALE TERMINAL ONLY, 12089040 OR EQUIVALENT.
2. USE CABLE SEAL 12015323 OR EQUIVALENT.
3. MATING PART - DEVICE
4. WHEN PARTS ARE SHIPPED, THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINERS MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.
5. SEALING CODE 3.
6. WHEN DESIGNING A PART TO MATE TO THIS WEATHER PACK CONNECTOR, REQUEST THE LATEST COPY OF DRAWING NUMBER 12020084 FROM THE PACKARD ELECTRIC DIVISION.
7. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSION)



STANDARD
CONSTRUCTION



OPTIONAL
CONSTRUCTION

CABLE END VIEW OF CONN BODY

Ulgraphics II		METRIC DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR: $\pm 2^\circ$	
		ONE PLACE ± 0.3 TWO PLACE ± 0.15	
CODE NO	QC	DES	
6900	-C-5110		
DWG DATE	17MY90	DR STEVE MARZO	17MY90
SCALE	2:1	CK STEVE MARZO	21MY90
REFERENCE NO	12103450 "A0" SIZE	APPR A.R. HERMANN	24MY90
MATERIAL SPEC		VOL CM ³	
SEE DRAWING			
NAME			
ASM CONN 3M W/P TWR			
PART NUMBER		SIZE	
1210 3452		A2	

PART NO	REV	STATUS	CONN BODY	APPLICATION	REF: TERMINAL/GENDER	MATING PART
12103451	A		12103449	DEVICE	12089040/MALE	DEVICE
12020403	A		12020194	DEVICE	12089040/MALE	DEVICE

PART NO
1210 3452

1210 3452