

E2340KSOG1

Size	3.40"	inch
Resolution	456(H) x 392(V)	pixel
Active Area	65.436(H) x 56.252(V)	mm
Outline Dimension	72.5(H) x 69.0(V) x 0.8 (T)	mm
Pixel Density	177	dpi
Display Colors	Black / White	
Surface Treatment	Anti-Glare	
Operation Temperature	-15~60	°C
Weight	8.0	g

