



All dimensions in mm

SPECIFICATIONS	
Inductance	Pin 1-2: 1300 $\mu$ H $\pm$ 35%
	Pin 3-4: 1300 $\mu$ H $\pm$ 35%
	Test Condition: 100KHz/100mV
Impedance	DCR(Max):40m $\Omega$
Rated Current	4.7A
Recommended Through Hole	1.0 mm