


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/04/09	A.D.M.
B	ECO #7722	09/25/09	A.D.M.




NOTES:

1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

1. BODY = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .000050 TO .00010 STRESS FREE NICKEL PER QQ-N-290.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

Property of Radiall Incorporated
This document cannot be reproduced or
communicated to a third party without prior
written permission of RADIALl Incorporated.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: A.D.M.	DATE 09/04/09	 APPLIED ENGINEERING PRODUCTS 104 John W. Murphy Dr. New Haven, CT 06513	
		CHKD: D.N.	DATE 09/04/09		
DECIMAL	ANGLE	APVD: J.M.	DATE 09/04/09	SMA STRAIGHT JACK P.C.B. MOUNT RECEPTACLE	
REFERENCE: 2009-08-3853 ORIGINATED: A.D.M. DATE: 09/04/09		MATERIALS & FINISHES: SEE NOTES		SIZE A	FSCM NO. 19505
				DWG NO. 9650-1113-064	REV B
		SCALE 5:1		THIRD ANGLE PROJECTION	
				SHEET 1 OF 1	

9650-1113-064