



USB3-A-S-S-TH


USB3-A, USB3-B SERIES

USB 3.0 INTERFACES

USB3-A Mates with:
USBC3-AM

USB3-B Mates with:
USBC3-BM

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?USB3-A or www.samtec.com?USB3-B

Insulator Material:

Nylon 6T Blue

Contact Material:

Phosphor Copper

Plating:

Au or Sn over 50µ" (1,27µm) Ni

Shield Plating:

50µ" (1,27µm) Ni

Front Shield:

Phosphor Copper

Back Shield:

Brass

Operating Temp Range:

-50°C to +85°C

Current Rating:

1.8 A per power (VBUS)

contact and ground contact,

0.25A per other contact

Voltage Rating:

100 VAC

Contact Resistance:

30 mΩ max power and ground,

50 mΩ max for other contact

Minimum Cycles:

5000

RoHS Compliant:

Yes

USB3
A
S
PLATING
TERMINATION
-F




= Gold Flash on Mating Area, Matte Tin on Tails

-S

= 30µ" (0,76µm) Gold on Mating Area, Matte Tin on Tails

-TH

= Through-hole


USB3
B
S
PLATING
TERMINATION
-F




= Gold Flash on Mating Area, Matte Tin on Tails

-S

= 30µ" (0,76µm) Gold on Mating Area, Matte Tin on Tails

-TH

= Through-hole



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683