

## **A13-65/ 65B/ 65C**



### FEATURES

- \* RATING: 20A max 12V DC
- \* MATERIAL OF SOCKET
  - Housing: nylon (UL 94V-2).
  - Inner contact: nickel plated metal.
  - Contact: nickel plated metal.
- \* **A13-65**: Snap-in lighter socket with dust-proof cover.
- \* **A13-65B**: Panel mount light socket with dust-proof cover.
- \* **A13-65C**: Snap-in light socket with dust-proof cover, without hole & wire.
- \* Fits with  $\varnothing$  21mm plugs.
- \* 10A fits wire 18 AWG.
- \* 15A fits wire 16 AWG.
- \* 20A fits wire 12 AWG.

