


R3-28C



 (4.8mm)0.187"
Quick connect

15A 250V AC
4.5mm MAX

FEATURES:

- Material:
Frame and cap: PBT(UL flame: 94V-0).
Terminal: tin plated brass.
- Mounted by nut.

CAP

Screw type

FUSE 

Ø 6.35*30mm

Ø 6.35*31.8mm

CUT-OUT

