




Rating	21A 14V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	2P SPST-NC		

*Material:

- 1.Frame: Nylon-66 (94V-2).
- 2.Pushbutton: PC
- 3.Bottom: Nylon-66 (94V-2).
- 4.Terminal: Silver plated copper.
- 5.Waterproof gasket : Epdm.

*Sealed: IP56 when supplied with panel seal.



Tolerance: ±0.3mm unless otherwise specified.

Date	Name	Description	No.
Drawn	Checked	Approved	SCI BOM No.
Jam Chan			1910101
11/22/18			Customer No.
			Model Name
			Emergency Stop Switch
			Model No.
			R13-930S-01-BR
			Rev.
			0
			Unit
			mm
			Shin Chin Industrial Co., Ltd.