





Rating	10A 250V AC		Mounting Hole
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1000V 1 minute		
Fuse Size	ø5.0*20mm		

Material:
Housing: Black, PF
Top cap: Black, PF
Terminals: Nickel Plated Brass



Tolerances ± 0.3 Unless Otherwise Specified

									△
									△
Date	Name	Description						No.	
Drawn	Checked	Approved	SCI BOM No	1310927	Model Name	FUSE HOLDER			
袁浩徐			Customer No	112-R3-12E	Model No.	R3-12E		Rev.	
09/24/19		178-19	Unit	mm	Shin Chin Industrial Co., Ltd.				0