




Rating	10A 250V AC	C $\frac{9A}{10A}$ US	Mounting Hole	Circuit Diagram
Insulation Resistance	DC 500V 100M ohm Min			Nil
Dielectric Strength	AC 1500V 1 minute			
Fuse Size	Ø6.4*30			



Material:
Housing: Black,PF
Top cap: Black, PF
Terminals: Nickel Plated Brass



Tolerances Unless Otherwise Specified ± 0.3 mm

Date	Name	Description	No.						
Drawn	Checked	Approved	SCI BOM No.	1310928	Model Name	FUSE HOLDER			
袁浩徐		Smican	Customer No.	112-R3-13E	Model No.	R3-13E		Rev.	
09/24/19		10/8-19	Unit	mm	Shin Chin Industrial Co., Ltd.			0	