




Rating	10A 125V AC 6.3A 250V AC 1.6W	UL US CSA	Mounting Hole 
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 Minute		
Fuse Size	Ø5*20mm(0.197"*0.788")		

Material:
Frame:Black,Nylon#66(94V-0)
Cover:Black,Nylon#66(94V-0)
Terminal:Silver plated,Copper alloy



Tolerances ± 0.3 Unless Otherwise Specified

Date	Name		Description					No.	
Drawn	Checked	Approved	SCI BOM No.	1310936	Model Name	FUSE HOLDER			
袁浩徐		Simon	Customer No.	112-R3-54B	Model No.	R3-54B		Rev.	
09/24/'19		10/8-19	Unit	mm		Shin Chin Industrial Co., Ltd.		0	