



Rating	10A 250V AC 	Mounting Hole 
Insulation Resistance	DC 500V 100M ohm Min	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-20°C~85°C	
Fuse Size	Ø5*20 mm	



Print no special orientation

Material:


Housing: Black, PF

Knob: Black, PBT


Knob cover: Red, ABS

Terminals: Tin Plated Brass

Printed: White, Hot stamping



Tolerances ± 0.3 Unless Otherwise Specified

								△
								△
Date	Name	Description						No.
Drawn	Checked	Approved	SCI BOM No	1310931	Model Name	FUSE HOLDER		
袁浩徐			Customer No	112-R3-78A-2N4-R	Model No.	R3-78A-2N4		Rev.
09/24/19		10/8-19	Unit	mm	Shin Chin Industrial Co., Ltd.			0