


Rating	300mA
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Yellow

*Material:
 Handle: ABS.
 Clip: Phosphor bronze.
 *Fits O.D. less than $\phi 2\text{mm}$ wire by soldering.



									△
									△
Date	Name	Description							No.
Drawn	Checked	Approved	SCI BOM No.	1510058		Model Name	IC CLIP		
柳新強	張子明	Simon	Customer No.			Model No.	R8-16F-Y		Rev.
06/12/15	7/2-15	7/8-15	Unit	mm	Shin Chin Industrial Co., Ltd.				0