








Rating	10A 28VDC   US T85	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C ~ 85°C		
Switch Function	3P SPST ON-OFF (LED dependent)		






*MATERIAL:
Frame: Nylon 66
Actuator: PC,
Waterproof rubber: Silicone
Terminals: Silver plated, Copper alloy
Hot Stamping: None
Waterproof: IP65



COLOR	Frame	Actuator	Waterproof rubber
SCI BOM NO.			
1824022	Black	Amber clear	Black
1824023	Black	Blue clear	Black
1824024	Black	Green clear	Black



Tolerances ±0.3 Unless Otherwise Specified

04/02/'18	曾敏捷	10A 28VDC通過UL61058/Demko,追加安規符號刻字				△	
08/04/'16	曹盈芳	依公司規定追加SCI Logo, 本體Rating改為10A 28VDC				△	
Date	Name	Description				NO	
Drawn	Checked	Approved	SCI BOM NO.	SEE TABLE	Model Name	ROCKER SWITCH	
曾敏捷			Customer No.	112-13112B802BY24VDC	Model No.	R13-112B8-02	Rev.
04/02/'18			Unit	mm	Shin Chin Industrial Co., Ltd.		2