





Rating	Input:DC12V/24V Output:DC5V 1Amp
Insulation R	DC: 500V 100M Min
Operation Temperature	-30~70°C
Circuit	Ste offaou
Fuse	2A mini blade fuse

原稿

Tolerance ± 0.3 unless specified notice

1250747
1250634

							△
							△
Date	Name	Description					NO
Draw	Check	Approval	SCI No.			Model Name	USB SOCKET
方 婷 鳳	蘇司辰	蘇司辰	Customer No.	112-A13-117C		Model No.	A13-117C
05/07/'09	5/7/09	7/17/09	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		