


Rating	Input:DC12V/24V
USB Rating	5V DC 2.1A Max
Insulation Resistance	DC:500V 100M Min
Operation Temperature	-20~+60°C
Fuse	2A mini blade fuse



Tolerance ± 0.3 unless specified notice

10/13/15	歐海金	修正圖面及編碼 (A13-117C->A13-117D)				△	
Date	Name	Descriptions				NO	
Drawn	Checked	Approved	SCI BOM No.	1251181	Model Name	USB Socket	
歐海金		<i>Shin</i>	Customer No.	112-A13-117D	Model No.	A13-117D	REV.
10/13/15		10/24-15	Unit	mm	Shin Chin Industrial Co., Ltd.		1