


Rating	Input: DC 12V/24V Output: DC 5V 0.5 Amp
Insulation Resistance	DC: 500V 100M Min
Operation Temperature	0~45° C
Circuit	Ste Affaou
Fuse	2A Mini Blade Fuse



Tolerances ± 0.3 Unless Otherwise Specified

△

△

No.

Date

Name

Description

Drawn

Checked

Approved

SCI BOM No.

1250431

Model Name

Car USB

雷云飛

歐陽安

李元生

Customer No.

112-A13-117

Model No.

A13-117

Rev.

05/28/'11

06/11/'11

06/11/'11

Unit

mm



Shin Chin Industrial Co., Ltd.

0