


Rating	13.6V DC 10A Max
Insulation Resistance	DC 500V 100MΩ Min
Voltage Breakdown	AC 1000V 1minute
Operating Temperature	-0°C~60°C

*.CIGAR LIGHTER LIGHTING TIME :25±5 SECS



			△	Drawn	Checked	Approved	SCI BOM No.	1251328	Model Name	Triple outlet socket	
			△	方婷鳳			Customer No.	112-A13-123B	Model No.	A13-123B	REV.
Date	Name	Description	NO	02/26/15			Unit	mm	Shin Chin Industrial Co., Ltd.		0