


Rating	12-24V DC, 10A Max
USB Rating	5V DC 2.1A+2.1A
Insulation Resistance	DC 500V 100MΩ Min
Voltage Breakdown	AC 1000V 1minute
Operation Temperature	0~45°C
Operation force to plug-in/pull-out	2~10Kgf
Fuse	10A



Tolerances ±0.3 Unless Otherwise Specified

Drawn	Checked	Approved	SCI BOM No	1251337	Model Name	DC-DC ADAPTER	Rev.
李景山		<i>Smc</i>	Customer No	112-A13-123C	Model No.	A13-123C	0
03/22/21		3/31/21	Unit	mm	Shin Chin Industrial Co., Ltd.		

Date	Name	Description	No.
------	------	-------------	-----