





Rating	12-24V DC 10A Max
USB Rating 	1.0A*2, 2A Max 5VDC
Insulation Resistance	DC 500V 100MΩ Min
Voltage Breakdown	AC 1000V 1minute
Operation Temperature	-0°C~60°C



Tolerances ± 0.3 Unless Otherwise Specified

08/08/13	方婷鳳	USB提升2A,修正外觀規格.	
12/07/11	李文彬	依照圖紙要求套用新圖框并修改雙層USB方向	
01/13/11	方婷鳳	USB upgrade to 2A max	
02/06/10	方婷鳳	Added USB rating	
Date	Name	Description	No.

Drawn	Checked	Approved	SCI BOM No.	1250662	Model Name	DC-DC ADAPTER	2
方婷鳳			Customer No.	112-A13-123	Model No.	A13-123	Rev.
08/08/13			Unit	mm	 Shin Chin Industrial Co., Ltd.		4