







Rating	12V 10A Max
USB Rating	5V DC 2.1A
Insulation Resistance	DC 500V 100M Min
Dielectric Strength	AC 1000V 1minute
Operation Temperature	0°C-45°C

Tolerances ± 0.3 Unless Otherwise Specified

Drawn	Checked	Approved	SCI BOM No.	1251387	Model Name	SOCKET	
劉嘉麗	黃洋	Simon	Customer No.	112-A13-124U	Model No.	A13-124U	Rev.
Date	Name	Description	No.	01/29/15	11/19/15	11/24/15	0
				Unit	mm	Shin Chin Industrial Co., Ltd.	