





Rating	Input 12V/24 DC Output 5V±0.25DC 2.5Amax. One Port Output 2.5A max.
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100M Min
Dielectric Strength	AC 1500V 1minute
Operation Temperature	0~60°
Operation Force To Plug-in/Pull-out	3~10 kgf
Fuse	3A Mini Blade



Material OF PLUG
Housing: ABS(UL flame:94V-HB 105° C)
Top Contact: Nickel Plated Brass.
Spring Contact: Nickel Plated Spring Steel.



Tolerances ± 0.3 Unless Otherwise Specified

Drawn	Checked	Approved	SCI BOM No.	1251180	Model Name	USB Twin Port Charger	
邱權		<i>Simon</i>	Customer No.	112-A13-164D	Model No.	A13-164D	Rev.
Date	Name	Description	No.	06/03/13	Unit	mm	0
						Shin Chin Industrial Co., Ltd.	

A3