





Rating	Input 12V/24V DC
	DC Socket 12V/24V 10A Max
	USB Output 5V DC 2.1A+2.1A max.
Insulation Resistance	DC 500V 100M ohm Min
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	0C°~45C°
Operation force to plug-in/pull-out	2~10Kgf
Fuse	10A

7 Positions adjustable plug



Tolerances ± 0.3 Unless Otherwise Specified

A3

Date	Name	Description	△	NO	Drawn	Checked	Approved	SCI BOM No.	1251336	Model Name	USB car socket	REV.
					李景山		Shing	Customer No.	112-A13-177B	Model No.	A13-177B	0
					03/22/'21		3/31/21	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		