





Rating	DC 12V/24V 10A
	Output 5V±0.25DC 2Amax.
	One port Output 2A max.
Insulation Resistance	DC 500V 100M ohm Min
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-0°C~60°C
Operation force to plug-in/pull-out	3~10Kgf
Fuse	10A



7 Positions adjustable plug



MATERIAL OF SOCKET

Housing:ABS

Inner contact: nickel plated brass.

Contact:nickel plated metal.

MATERIAL OF PLUG

Housing:PBT

Top contact:nickel plated brass.

Spring contact:nickel plated spring steel.

A3

Date	Name	Description	△	Drawn	Checked	Approved	SCI BOM No.	Model Name	USB car socket	REV.
			△	DAVID SU	100.3.23		Customer No.	112-A13-177	Model No.	A13-177
			NO	3/22/11			Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	