











Rating	Input	12/24 VDC
	Output	USB socket - 5V 4.2A max.
Insulation Resistance		DC 500V 100M ohm Min.
Operation Temperature		-20°C~60°C



							△
							△
Date	Name	Descriptions					NO
Drawing	Check	Approval	SCI No.	1251343		Model Name	USB socket
DAVID SU			Customer No.	112-A13-203C		Model No.	A13-203C
07/06/16'			Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		