






Rating	DC Input : 12~24V Output1 : 5V/2.1A Total Double USB OUTPUT2: 12V 5A
Insulation Resistance	DC 500V 100M ohm Min.
Operation Temperature	-20° C~45° C
Fuse	8A
Color	White



Tolerances ± 0.3 Unless Otherwise Specified

						△	
						△	
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No	1251394	Model Name	LIGHTER PLUG	
黃洋	黃洋	Simon	Customer No	112-A13-215	Model No.	A13-215	Rev.
07/16/15	4/12-16	4/13-16	Unit	mm	Shin Chin Industrial Co., Ltd.		0