



1. RATING: 12V, MAX 10A
2. CIGAR LIGHTER LIGHTING TIME :25±5 SECS

Rating	12V 10A Max
Insulation Resistance	DC 500V 100M ohm Min
Voltage Breakdown	AC 1000V 1 mintue
Operation Temperature	-20°~60°



05/09/16	劉嘉麗	增加DATE CODE	△	Drawn	Checked	Approved	SCI BOM No.	1250055	Model Name	TWIN OUTLET ADAPTER
Date	Name	Description	No.	05/09/16	5/11/16	5/11/16	Customer No.	112-A13-39B	Model No.	A13-39B
							Unit	mm	Shin Chin Industrial Co., Ltd.	Rev. 1

1250055