






Rating	12V 10A Max
USB Rating	5V DC 2.1A
Insulation Resistance	DC 500V 100M Min
Dielectric Strength	AC 1000V 1minute
Operation Temperature	0°C~45°C



Blue LED



Tolerances ± 0.3 Unless Otherwise Specified

			△	Drawn	Checked	Approved	SCI BOM No.	1251385	Model Name	SOCKET	
			△	劉嘉麗	黃洋	研發部	Customer No.	112-A13-39U	Model No.	A13-39U	Rev.
Date	Name	Description	No.	03/20/15	4/1/15	11-12 李元生	Unit	mm	Shin Chin Industrial Co., Ltd.		0