





Rating	DC 13.6V 10A Max
Insulation Resistance	DC 500V 100M Ω Min
Voltage Breakdown	AC 1000V 1minute
Operating Temperature	-20°C~65°C



1. RATING: DC 13.6V, MAX 10A

				Drawing	Check	Approval	SCI No.	A13-49A	Model Name	
△	05/30/02	華	CI/PDM/A13/A13-49/A13-49A	蘇新良		王作山	Customer No.	112-A13-49A	Model No.	
△	Date	Name	Descriptions	7/1/02		王作山	Unit		SHIN CHIN INDUSTRIAL CO., LTD.	