


Rating	Input 12V DC
	DC Socket 12V 10A Total Max.
	USB Output:5V±0.25DC 2.1A Total Max
Insulation Resistance	DC 500V 100M Min
Operation Temperature	0~45° C
Operation force to plug-in/pull-out	2~10Kgf
Fuse	10A glass tube



1. RATING: 12V,10A MAX
2. CIGAR LIGHTER LIGHTING TIME :25±5 SECS

				Drawing Check	Approval	SCI No.		Model Name	Multi Outlet Adapter
				104.4.17 蘇永民	宋永民 8/15	Customer No.	112-A13-49U	Model No.	A13-49U
△	Date	Name	Descriptions			Unit		SHIN CHIN INDUSTRIAL CO., LTD.	