



Rating	Input	13.6V DC
	Output	Total Output:15A max. USB sockets - 5V 2.1A max.
Insulation Resistance		DC 500V 100M ohm Min
Voltage Breakdown		AC 1000V 1minute
Operating temperature		-20°c~60°c



可旋轉(0°--180°)



					△	
Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1251388	Model Name	
葉志偉		<i>Simon</i>	Customer No.	112-A13-97U	Model No.	A13-97U
07/17/15		9/8-15	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 0