



Rating	Input:12V/24 DC Output:USB Socket - 5V 2.1A max. Auto Sockets - 20A max.
Insulation Resistance	DC 500V 100MΩ Min.
Dielectric Strength	AC 1500V 1 minute
Operating Temperature	-0℃~60℃


 Screw in Bulk
 Ø3*16



1.Tolerances ± 0.3 Unless Otherwise Specified

Drawn	Checked	Approved	SCI BOM No.	1251121	Model Name	Double socket
DAVID	102.1.24	102.1.24	Customer No.		Model No.	A13-142194BHD-BB3
Date	Name	Description	No.	2013/1/19	Unit	mm
						Shin Chin Industrial Co., Ltd.
						Rev. 0