

Rating	Input	12-24 V DC
	Output	USB+Micro USB - 5V 2.4A max.
Insulation Resistance		DC 500V 100M ohm Min.
Operation Temperature		-20°C~45°C
Operation Force to plug-in/pull-out		2~10Kgf
Fuse		3A glass tube

MATERIAL OF PLUG:


Housing: ABS, white (UL flame:94V-HB).

Cover:ABS, Black. (UL flame:94V-HB).

Led: Blue.

Top contact: nickel plated brass.

Spring contact: nickel plated spring steel.



						△	
						△	
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1251501	Model Name	Lighter Plug	
Jam Chan	8/20/16	王作山	Customer No.		Model No.	A13-201B1-M	Rev.
2/4/16	8/20/16	8/24/16	Unit	mm	Shin Chin Industrial Co., Ltd.		0