







Rating	Input: 6V~33V DC Voltage Tolerance: $\pm 1\%$ (0.1V @ 12V, 0.2V @ 24V) LED display. Reverse polarity protection Surge protection up to 400W/35V	Mounting Hole 
Insulation Resistance	DC 500V 100M Ω Min.	
Operating Temperature	-20 $^{\circ}$ C~50 $^{\circ}$ C	



Tolerances ± 0.3 Unless Otherwise Specified

Tolerances 20% Unless Otherwise Specified				Drawn	Checked	Approved	SCI BOM No.	1570002	Model Name	DC Voltmeter	
			△	Rock Hsu	1.04		Customer No.		Model No.	A25-1-BB3-G	Rev.
			△	12/31/15	蘇承民		Unit	mm	Shin Chin Industrial Co., Ltd.		0
Date	Name	Description	No.								