









Rating	Operating voltage:7V~33V DC Measuring Current range:0~25.0A Current Tolerance: 1A:±0.1A,10A:±0.5A,25A:±1.5A LED display. Reverse polarity protection.Surge protection up to 400W/35V	Mounting Hole 
	Insulation Resistance	
	Operating Temperature	
	DC 500V 100MΩ Min.	
	-20℃~50℃	



Tolerances ±0.3 Unless Otherwise Specified

for SCI

Date	Name	Description	No.	Drawn	Checked	Approved	SCI BOM No.	1570026	Model Name	DC Ammeter	
				Rock Hsu			Customer No.		Model No.	A25-1D-BB3-U	Rev.
09/14/17							Unit	mm	Shin Chin Industrial Co., Ltd.		0