



Rating	12/24V DC
Operating voltage range	9.9V~16.2V DC
	20V~32.1V DC
Insulation Resistance	DC 500V 100MΩ Min
Operation Temperature	-20°C~+60°C



12V/24V Battery Check	Charger Check		Alternator Check		12V/24V Battery Check				Cranking Check
	12V VOLTAGE	24V VOLTAGE	RED	RED	100% GREEN	80% YELLOW	60% ORANGE	40% RED	
14.8V~16.2V		29.6V~32.1V	●		●				●
13.7V~15.1V		27.4V~30.0V		●	●				●
12.7V~16.2V		25.4V~32.1V			●				●
12.3V~13.0V		24.6V~25.8V				●			●
11.8V~12.6V		23.6V~25.0V					●		●
11.1V~12.1V		22.6V~24.0V						●	●
09.9V~32.1V									●

A4

04/20/17	陳永賜	因應相關電壓測試仍有部分誤差值較大修改電壓以符合測試				△
Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1570007	Model Name	Battery tester
陳永賜			Customer No.		Model No.	A25-2A
04/20/17			Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 1