











Rating	Operating voltage: 7V-33V DC $\pm 2\%$ (0.24V @ 12V, 0.48V @ 24V) Measuring Voltage: 7-33V Long time use suggestion to 0-70A Measuring Current range: 0-100.0A $\pm 3\%$ 10A ± 0.3 A, 50A ± 1.5 A, 100A ± 3.0 A LED digital display. Reverse polarity protection. Surge protection up to 400W/36V	Mounting Hole
Insulation Resistance	DC 500V 100M Ω Min.	
Operating Temperature	-20 $^{\circ}$ C~50 $^{\circ}$ C	



原稿
2018.7.19
研發部



Tolerances ± 0.5 Unless Otherwise Specified

				Drawn	Checked	Approved	SCI BOM No.	1570035	Model Name	DC Volt / Amp meter	
				Rock Hsu			Customer No.	112-A25-7-BB3-G	Model No.	A25-7-BB3-G	Rev.
Date	Name	Description	No.	06/26/18		6/26/18	Unit	mm	Shin Chin Industrial Co., Ltd.		0

for SCI