



(55 SERIES) PA1







Rating
6A 125V AC 3A 250V AC
Contact resistance
50mΩ Max
Insulation resistant
DC 500V 100MΩ Min
Dielectric strength
AC 1000V 1 minute
Cut out
 4 mm max

FEATURES

- * MATERIAL: Phenolic base (UL flame: 94V-0).
- * Contacts and Terminals are copper with silver alloy and silver plated.
- * Epoxy sealed for dust and moisture resistant.

PA1

FUNCTION	BUTTON	TERMINAL
 0 1 OFF 2P SPST ON	 A	1  SO 2  PC 3  PC Angle(2.54) 5  PC Angle(3.8)
 0 2 ON 3P SPDT ON		
 0 6 (ON) 3P SPDT ON		