



Rating	3A 125V AC 1.5A 250V AC		Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1000V 1 minute			
Button	$\phi 6 \times 5.6$			
Switch Function	2P SPST OFF-(ON)			


Material:

Button: Black,ABS

Bushing: Aluminum Alloy

1 HEX NUT ASSY

1 SPRING WASHER ASSY



Special specification For Radio Shack only
1、Tolerances ± 0.3 Unless Otherwise Specified

02/15/'23	曾敏捷	依SCI決議修改校正記事說明					
09/05/'22	曾敏捷	依ECR(JHF20220824-104),尺寸由9.0改為9.6,3.1改為2.5					
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1830775	Model Name	PUSH SWITCH	
曾敏捷	符列迎	李理	Customer No.	112-R13-24A-B	Model No.	R13-24A-05	Rev.
02/15/'23	2023/03/14	2023/03/15	Unit	mm	 Shin Chin Industrial Co., Ltd.		2