






Rating	1.5A 250VAC, 3A 125VAC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST OFF-(ON)		

Material:
Frame: Black, ABS
Actuator: Black, ABS
Base: Black, PF
Printed: None



For 玖新

Tolerances ± 0.3 Unless Otherwise Specified

09/01/'21	曾敏捷	依ECR(RAD20210824-393)外觀圖恢復刻字標示,去除刻字圖號標示		
03/31/'21	曾敏捷	外觀圖取消安規刻字,增加刻字圖圖號標示		
03/05/'20	曾敏捷	依ECR(RAD20200110-015)增加R13-40型號鐫雕		
Date	Name	Description	No.	
Drawn	Checked	Approved	SCI BOM No.	1830730
Model Name	PUSH SWITCH	Customer No.	112-R13-40A-B	Model No.
R13-40A-05	Rev.	3	Shin Chin Industrial Co., Ltd.	