








Rating	8A 125V AC 1/3HP 8A 250V AC 1/2HP SC us	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST ON-OFF		



1 HEX NUT ASSY
1 SPRING WASHER ASSY
1 KNURL NUT ASSY



Tolerances Unless Otherwise Specified ± 0.5

06/27/'12	羅 斌	更新圖框,增加SCI LOGO.					△
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	1810565	Model Name	TOGGLE SWITCH	
羅 斌			Customer No.	112-R13-412A2	Model No.	R13-412A2-02-HWR	Rev.
06/27/'12			Unit	mm	Shin Chin Industrial Co., Ltd.		1