







Rating	8A 125V AC 1/3HP 8A 250V AC 1/2HP 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	3P SPDT ON-ON		



1 HEX NUT ASSY
1 SPRING WASHER ASSY
1 KNURL NUT ASSY



Tolerances Unless Otherwise Specified ± 0.5

									△
									△
Date	Name			Description					No.
Drawn	Checked	Approved	SCI BOM No.	1810566	Model Name	TOGGLE SWITCH			
曹盈芳			Customer No.	112-R13-412C2	Model No.	R13-412C2-02-HWR	Rev.		
03/15/17		3/15/17	Unit	mm	 Shin Chin Industrial Co., Ltd.				0