







Rating	8A 125V AC 1/3HP 8A 250V AC 1/2HP 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	3P SPDT ON-OFF-ON		



1 HEX NUT ASSY
1 SPRING WASHER ASSY
1 KNURL NUT ASSY



Tolerances Unless Otherwise Specified ± 0.5

06/27/'12	羅 斌	更新圖框,增加SCI LOGO.				△	
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1810567	Model Name	TOGGLE SWITCH	
羅 斌			Customer No.	112-R13-412D2	Model No.	R13-412D2-02-HWR	Rev.
06/27/'12			Unit	mm	 Shin Chin Industrial Co., Ltd.		1