








Rating	6A 250V , 10A 125V AC 		
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST ON-OFF		



Material:
Frame: Black, PF
Actuator: Black, Nylon#66
Hot stamping: White, ●



Tolerances ± 0.3 Unless Otherwise Specified

09/09/'21	曾敏捷	依ECR(RAD20210824-393)外觀圖恢復刻字標示,去除刻字圖號標示			③	
04/19/'21	曾敏捷	外觀圖取消安規標示,增加刻字圖號標示			②	
01/04/'16	何坤	為滿足安規要求,追加品名及SCI Logo,并更新圖面			①	
Date	Name	Description			No.	
Drawn	Checked	Approved	SCI BOM No.	1824497	Model Name	ROCKER SWITCH
曾敏捷	符列亞	李理	Customer No.	112-R13-49A-B/B	Model No.	R13-49A-05
09/09/'21	2021/10/07	2021/10/11	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 3